

PURCHASE ORDER

QR-ADMPPS-04

INDUSTRIAL TECHNOLOGY DEVELOPMENT INSTITUTE

DOST Compound, Gen. Santos Ave., Bicutan, Taguig City
DOST Trunkline: 837-2071 local 2220 / 2221

13. 256 GF





Supplier:	ASPEN MULTI-SYSTEM CORPORATION	P.O. No.:	GF-E-243-2013
Address:	Unit D5 Lui Gin Condo, Manila East Road El Monteverde Subd., Brgy. San Juan, Taytay, Rizal	Date:	June 13, 2013
		Mode of Procurement:	Public Bidding
PO-08-3		PR #	04-2013-0022
		ASC #	262-2013

Gentlemen:
Please furnish this office the following articles to the terms and conditions contained herein:

Place of Delivery:	Metrology Bldg. (not later than 3:00 P.M.)	Delivery Term:	Forty (45) calendar days
Date of Delivery:		Payment Term:	

Stock No.	Unit	Description	Quantity	Unit Cost	Amount
1	unit	BIOHAZARD SAFETY CABINET JCSB-1500SB CLASS II TYPE A2 Safety Class : Class II Type A2 Filtration : Aluminum Frame <b style="padding-left: 20px;">Mini Pleated HEPA Filter <b style="padding-left: 20px;">Optical ULPA Filter Efficiency : 99.995% at 0.3um particles Control : Microprocessor Control <b style="padding-left: 20px;">9 Step Air Velocity Control Material : Stainless Steel 304 <b style="padding-left: 20px;">(AISI304) working chamber Sterilization : Germicidal UV Lamp w/timer <b style="padding-left: 20px;">Including Stand with Caster Dimensions : Inner - 1500W x 530D x 680H mm <b style="padding-left: 20px;">Outer - 1560W x 800D x 1990H mm HEPA Filter : 0.3 um Particle Removal 99.993% - <b style="padding-left: 20px;">99.995% / Inquire for optional ULPA Filter Aluminum frame mini-pleated type with wire mesh protection guard Air Circulation : 70% of HEPA filtered air re- circulation and 30% exhaust through HEPA filter Controller : Display - Back Light LCD Display <b style="padding-left: 20px;">Speed Control - 9 Step Air Velocity Control from <b style="padding-left: 40px;">0.3 - 0.6 m/sec. Lamp Control - FL Lamp ON/OFF/UV Lamp Timer/ <b style="padding-left: 20px;">Total Using Time	1	598,500.00	598,500.00

Page 1 of 2 pages

Conforms: <div style="text-align: center;">  <u>BENEDICTO BALON</u> (Signature over printed name) <u>7/1/13</u> (Date) </div>	Very Truly yours,  <u>DR. NUNA E. ALMANZOR</u> Director	Requisitioning Office/Dept.  <u>REYNALDO L. ESGUERRA</u> Chief-EBD	Funds Available:  <u>SOLEDAD S. REYES</u> Accountant IV	Amount 598,500.00 ALOBS No. <u>2013060855</u>
---	---	--	---	--

PURCHASE ORDER

QR-ADMPPS-04

INDUSTRIAL TECHNOLOGY DEVELOPMENT INSTITUTE

DOST Compound, Gen. Santos Ave., Bicutan, Taguig City
DOST Trunkline: 837-2071 local 2220 / 2221

13-25669

Supplier: ASPEN MULTI-SYSTEM CORPORATION	P.O. No.: GF-E-243-2013		
Address: <i>Unit D5 Lui Gin Condo, Manila East Road El Monteverde Subd., Brgy. San Juan, Taytay, Rizal</i>	Date: June 13, 2013	Mode of Procurement: Public Bidding	
	PR # 04-2013-0022	ASC #	262-2013

Gentlemen:
Please furnish this office the following articles to the terms and conditions contained herein:

Place of Delivery: Metrology Bldg. (not later than 3:00 P.M.)	Delivery Term: Forty five (45) calendar days
Date of Delivery:	Payment Term:

Stock No.	Unit	Description	Quantity	Unit Cost	Amount
		Balance Carried Forward			598,500.00
		Illumination Lamps : FL 30W x 2 ea			
		Germicidal UV Lamp : UV 30W x 1 ea			
		Utility : Gas Cock / Air Cock / Power Outlet 220V x 2 ea			
		Sash Door : Weight Balanced Sliding Tempered Safety Glass 5 mm Thick			
		Electrical Requirement : 220 VAC 50/60 Hz or 120 VAC 60Hz			
		Biohazard Class II Type A2 application			
		*Class II Type A2 design for personnel, product, sample, environment protection			
		*70% of total air re-circulates within the cabinet and 30% of air vent through HEPA filter to ambient			
		0.3 um Particle 99.993% Removal Efficiency			
		*Two Minipleat HEPA filters, which operates at a typical efficiency of 99.993% at 0.3um particles			
		*These filter provide a higher level of product and cross contamination protection			
		Back Light LCD Microprocessor Control			
		*9 step air velocity, FL, UV lamp on / off, timer, total using time alarm			
		Silent Fan Blower			
		*Noiseless and vibration free working environment			
		Weight Balanced Smooth Sliding Sash Door			
		*5mm thick tempered safety glass			
			Less: VAT	26,718.75	
			EWT	5,343.75	32,062.50
					566,437.50
			Accessories:		
			1 unit Spare Exhaust HEPA Filter for J30B-1500SE		
			1 unit Spare Main HEPA Filter for J30B-1500SE		
			1 set Germicidal UV Lamp 253 nm, 30 watt for J30B-1500SE		
			1 unit UPS		
			1 unit Magnetic Stirrer MSE-310N (3000)		
			1 unit Microcentrifuge K17-410 (3000)		
			1 unit Automatic Gas Burner		
			2 units Bacteriocinators		
			1 unit Lab Chair, stainless		
			1 unit Underbench cabinet		

Page 2 of 2 pages
(Total Amount in Words) *Five hundred sixty six thousand four hundred thirty seven pesos & 50/100*

In case of failure to make the full delivery within the time specified above, a penalty of one-tenth (1/10) of one percent for every day of delay shall be imposed.

Very Truly yours,
[Signature]
DR. NUNA E. ALMANZOR
Director

Conforme: *[Signature]*
BENEDICTO BRILON
(Signature over printed name)
7/11/13
(Date)

Requisitioning Office/Dept. <i>[Signature]</i> REYNALDO L. ESGUERRA Chief-EBD	Funds Available: <i>[Signature]</i> SOLEDAD S. REYES Accountant IV	Amount ALOBS No. <i>598,500.-</i> <i>20130608JT</i>
---	--	--